## shopvalves.com



## **Water Temperature Control - Recirculation Systems**

### **Digital**

# The Brain® Model DMC80-80BS



Digital technology provides enhanced water temperature control accuracy which resists zero system demand "Temperature Creep" without the use of a manual throttling valve or a temperature activated pump shut-off device (aquastat).

SAGE® (BS) available with specific ProtoCessor cards for BAS connectivity to systems which operate on Modbus TCP, BACnet $^{\text{\tiny{M}}}$ , or LonWorks $^{\text{\tiny{M}}}$  protocols.

Mobile connectivity features smart hot water system dashboard monitoring, secure remote programming, multi-location view, temperature and system diagnostic alerts, with unlimited digital documentation and automated report generation. Mobile connectivity may be enabled by a customer activated subscription.


### **Operational Specifications (DRV80)**


- +/-2°F DRV water temperature control at peak, moderate or zero fixture demand on hot water system designed for continuous recirculation
- 1°F minimum recirculating water temperature differential
- LCD display which indicates: set point, delivered temperature, error codes and alarm conditions capable of BAS and mobile connectivity
- Programmable set point range of 81-158°F (27-70°C) capable of BAS or mobile monitoring and adjustment
- Programmable thermal disinfection range of 158-185°F (70-85°C)
- Programmable 1st level hi/lo temp alarm display capable of BAS or mobile alerting
- Automatic safe closure of hot water inlet in response to: inlet supply failure, 110V power failure, or programmable high temperature error
- Automatic safe closure of hot water inlet powered by a replaceable lithium battery monitored for low-level alerting

#### Technical Specifications (DRV80)

- 100-240V AC
- · Polymer Electronics Enclosure
- · Stainless Steel Valve Construction
- Lead Free compliant
- Maximum inlet HW supply temperature 185°F (85°C)
- Minimum Continuous Recirculation 10 GPM (38 LPM) per DRV
- Minimum System Draw Off 0 GPM
- Conforms to ASSE 1017, CSA B125.3-11, UL E357437, and CE
- · Operational water pressure of 10-150 psig (.7-10 barg)
- Display in °C or °F
- SAGE® (BS) for BAS or Mobile Connectivity
- Shipping weight 1200 lbs (544.3 kg)

For a submittal drawing, refer to D40818





	Recirculation Systems - Digital (GPM and PSIG)									
	Model		Pressure D	rop (PSIG)		Minimum System Draw-Off	C <sub>v</sub>			
١	DMC80-80BS	5	10	15	20					
	GPM	188	266	326	376	0	84			

Recirculation Systems - Digital (LPM and BARG)									
Model		Pressure D	rop (BARG)		Minimum System Draw-Off	C			
DMC80-80BS	0.3	0.7	1.0	1.4	Willilliani System Diaw-On	υ <sub>ν</sub>			
LPM	711.7	1006.9	1234.0	1423.3	0	84			

Designs, materials, weights and performance ratings are approximate and subject to change without notice. Visit armstronginternational.com for up-to-date information.